

## Processing instructions

Shake well before use.

Application on the surface with a brush or a spray gun in a thin layer.

Evaporating time: 3-5 min

Polish carefully afterwards.

For new tools a 3 times-treatment with release agent is necessary to get a basic treatment.

After this basic procedure any requested treatments with release agents can be made.

## In General

T 03-01 is a very liquid well workable release agent.  
It is especially suitable for reactive systems.

Other liquid mould release waxes have a low boiling point (70°) which leads to sinking marks on the surface now and then. Since the boiling point of T 03-01 is very high (about 140°C), there aren't any sinking marks.

Moreover the release agent is hardly visible on the mould surface (dry surface).  
Any preparations for later lacquering are reduced manifold.

T 03-01 is especially suitable for prototyping and mould making.

Sales units: 1,000 l tin / 5,000 l can

## Storing

Keep away from sources of ignition

Do not store outdoors.

In case of extreme cold do stabilize to 15° C.

## Safety measure

Please follow the precaution instructions of the Government Safety Organisation of the chemical industry when working with this material. Please follow safety advices !

## Waste Disposal

According to arrangement with local authorities cured material can be disposed as domestic or commercial waste.

Non-cured products are waste which is subject to inspection and has to be disposed accordingly.

In case of further questions please do not hesitate to contact our Department for Product Safety.

The instructions and recommendations are given in good faith and are based on long experience and careful tests. Since the conditions of use are beyond our control, and due to versatility of applications and working methods, we can't give any guarantee. All information are non-binding and are no guarantee for special characteristics or properties of the product. Despite information given from **ebalta** the customer has to make his own tests regarding applications and processing. If any special warranty is requested, written agreement on this subject is essential.

ebalta UK Limited . B2 Langham Park, Trent Lane . Castle Donington . Derbyshire DE74 2UT  
t: +44 1332 814700 . f: +44 1332 814775 . e: info@ebalta.co.uk . w: www.ebalta.co.uk