

-UKBasis	High quality, very thin liquid fast casting resin system
Resin	SG 2000 Comp. A
Hardener	SG 2000 Comp. B
Colour	ivory

Applications

- Foundry patterns
- Core boxes
- Negatives
- Control castings
- Coping models
- Vacuum forming tools
- Mould probes for trimming of prototypes

Properties

- unfilled
- very thin liquid
- high filler content possible
- good curing
- very high strength
- very heat resistant

Processing data

Product		Mixture SG 2000 / Comp. A+B	Resin SG 2000 Comp. A	Hardener SG 2000 Comp. B
Colour		ivory	white	light yellow
Mixing ratio	p. b. w.		100	100
Viscosity at 25°C	mPas	50 ± 5	80 ± 10	25 ± 5
Density at 20°C	g / cm ³	1,10 ± 0,02	1,02 ± 0,02	1,14 ± 0,02
Pot life 200 g / 20°C	min.	2,5 - 3,5	-	-
Curing time at RT	hrs.	0,5 - 1	-	-

Physical data

Properties	Inspect. requirem.	Unit	Value
Flexural strength	EN ISO 178	MPa	57 ± 5
Flexural modulus	EN ISO 178	MPa	1500 ± 100
Flexural strength at breakage	EN ISO 178	%	7,5 ± 0,4
Compressive strength	EN ISO 604	MPa	45 ± 5
Impact resistance (Charpy)	EN ISO 179	kJ/m ²	24 ± 4
Heat resistance (HDT)	DIN EN ISO 75 B	°C	86 ± 3
Shore hardness	DIN 53505	Shore D	72 ± 2
Coefficient of linear expansion	DIN 53752	10 ⁻⁶ K ⁻¹	-
Linear shrinkage	internal	%	-

Sales units (packages)

Units	Resin	SG 2000 Comp. A	1,000 kg / 5,000 kg / 25,000 kg / 50,000 kg
	Hardener	SG 2000 Comp. B	1,000 kg / 5,000 kg / 25,000 kg / 50,000 kg

Processing instructions

The fillers should be stirred into the single components A and B , so that these have nearly the same viscosity. After that both components can be mixed very well.

In case of small quantities and sufficient experience it is also possible to mix the unfilled components first and then to stir in the filler, without making the potlife too short for casting.

In General

The product group **ebalta** SG 2000 consists of high-quality, nearly odourless two-component-Polyurethane casting resins without mixed in filler. The filler is stirred in when the components are mixed. There are different resin components available, which are processed with one hardener. The single types differ in potlife and curing time.

We have different resins -with one hardener- available. The various types differ in potlife and curing time:

SG 2000 S, potlife 1,5 – 2,5 minutes

SG 2000, potlife 2,5 – 3,5 minutes

SG 2000 L, potlife 7 – 8 minutes

SG 2015 potlife 14 - 18 minutes

The fast curing of the materials leads to a short demoulding time. The very thin binding agent effects a high filler content. The addition of different fillers determines the properties and strength.

Material should be carefully stirred up/ shaken before use.

Filler content and delivery form are mentioned on the separate mixing table.

The product can be subject to colour variations due to raw materials, but these colour variations have no influence on the quality and the properties of the product.

Storing

At room temperature (18 – 25°C) and closed original containers storage life is 6 months.

Partly used containers have always to be closed and the material has to be used up as soon as possible.

Safety measure

Please follow the precaution instructions of the Government Safety Organisation of the chemical industry when working with this material. Please follow safety advices !

Waste Disposal

According to arrangement with local authorities cured material can be disposed as domestic or commercial waste.

Non-cured products are waste which is subject to inspection and has to be disposed accordingly.

In case of further questions please do not hesitate to contact our Department for Product Safety.

The instructions and recommendations are given in good faith and are based on long experience and careful tests. Since the conditions of use are beyond our control, and due to versatility of applications and working methods, we can't give any guarantee. All information are non-binding and are no guarantee for special characteristics or properties of the product. Despite information given from **ebalta** the customer has to make his own tests regarding applications and processing. If any special warranty is requested, written agreement on this subject is essential.

ebalta UK Limited . B2 Langham Park, Trent Lane . Castle Donington . Derbyshire DE74 2UT
t: +44 1332 814700 . f: +44 1332 814775 . e: info@**ebalta**.co.uk . w: www.**ebalta**.co.uk